

MLL-H-946/400~800mW




**LOW NOISE INFRARED LASER
AT 946 nm**

All solid state low noise infrared laser at 946 nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in scientific experiment, optical instrument, optical sensor, measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	946±1
Output power (mW)	>400, 450, 500, ... ,800
Transverse mode	Near TEM ₀₀
Operating mode	CW
Power stability (rms, over 4 hours)	<1%, <2%, <3%, <5%
Noise of amplitude (rms, 20Hz~20MHz)	<1%
Warm-up time (minutes)	<10
M ² factor	<2.0
Beam divergence, full angle (mrad)	<2.0
Beam diameter at the aperture (mm)	~3.0
Beam height from base plate (mm)	29
Pointing stability after warm-up (mrad)	<0.05
Operating temperature (°C)	10~35
Power supply (90-264VAC)	PSU-H-FDA/PSU-H-OEM
Expected lifetime (hours)	10000
Warranty period	1 year



MLL-H-946	PSU-H-FDA	PSU-H-OEM
<p>154.5(L)×77(W)×60(H) mm³, 0.9 kg</p>	<p>275(L)×145(W)×104(H) mm³, 2.3 kg</p>	<p>245.5 (L) ×146(W) ×94 (H) mm³, 2.2 kg</p>