



MLL-III-1310L/1~10mW



LOW NOISE INFRARED  
DIODE LASER AT 1310nm

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are used in measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	1310±20	
Operating mode	CW	
Output power (mW)	>1, 2, 3, ..., 10	
Power stability (rms, over 4 hours)	<1%, <2%, <3%	
Transverse mode	Near TEM <sub>00</sub>	
Noise of amplitude(rms,20Hz~20MHz)	<1%	
Dimensions of beam at the aperture (mm)	~1.5	
Beam divergence, full angle (mrad)	<2.0	
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	24.8	
Operating temperature (°C)	10~35	
Power supply	85-264VAC	PSU-III-LED/ PSU-III-FDA (Frequency for 1Hz-30kHz)
	100-240VAC	PSU-A-D (Frequency for 30kHz -100kHz)
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz, 30kHz-100kHz optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



MLL-III-1310L	PSU-III-LED	PSU-III-FDA	PSU-A-D
<p>143.5(L)×73(W)×46.2(H) mm<sup>3</sup>, 0.7kg</p>	<p>188.6 (L) ×155(W) ×92 (H) mm<sup>3</sup>, 1.5kg</p>	<p>171(L) ×130(W) ×62.2 (H) mm<sup>3</sup>, 1.2kg</p>	<p>162(L) ×144(W) ×70 (H) mm<sup>3</sup>, 1.0kg</p>