



MLL-III-1560/1~1000mW

LOW NOISE INFRARED DIODE LASER AT 1560 nm





Low noise diode infrared laser module at 1560 nm, is made features of ultra compact, long lifetime, low cost and easy operating, which is used in measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	1560 ± 10		
Output power (mW)	>1, 100, 150, 200, ..., 1000		
Transverse mode	Near TE ₀₀		
Operating mode	CW		
Power stability (rms, over 4 hours)	<1%, <3%, <5%		
Noise of amplitude(rms,1~20MHz)	<1%		
Warm-up time (minutes)	<5		
M ² factor	<20		
Beam divergence, full angle (mrad)	<3.0		
Dimensions of beam at the aperture (mm)	~5×8		
Beam height from base plate (mm)	24.8		
Polarization ratio	>50:1		
Pointing stability after warm-up (mrad)	<0.05		
Operating temperature (°C)	10~35		
Power supply (90-264VAC or 5VDC)	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
Expected lifetime (hours)	10000		
Warranty	1 year		



MxL-III-1560	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
 136(L)×73(W)×46.2(H) mm ³ , 0.6kg	 153 (L) ×155(W) ×92 (H) mm ³ , 1.5kg	 133 (L) ×130(W) ×65 (H) mm ³ , 1.2kg	 100 (L) ×62(W) ×56 (H) mm ³ , 0.2kg
