



MLL-III-543/1~100mW

**LOW NOISE GREEN LASER
AT 543 nm**

Low noise green laser at 543 nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in scientific experiment, optical sensor, measurement, instrument, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	543 ± 1		
Output power (mW)	>1, 5, 10, 20, ... , 100		
Transverse mode	TEM ₀₀		
Operating mode	CW		
Power stability (rms, over 4 hours)	<1%, <3%, <5%		
Noise of amplitude (rms, 1~20MHz)	<1%		
Warm-up time (minutes)	<10		
M ² factor	<1.2		
Beam divergence, full angle (mrad)	<1.5		
Beam diameter at the aperture (mm)	~2.0		
Beam height from base plate (mm)	24.8		
Polarization ratio	>100:1 (0 or 90 degree)		
Pointing stability after warm-up (mrad)	<0.05		
Operating temperature (°C)	10~35		
Power supply (90-264VAC or 5VDC)	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
Expected lifetime (hours)	10000		
Warranty	1 year		



MxL-III-543	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
<p>140.8(L)×73(W)×46.2(H) mm³, 0.6kg</p>	<p>154 (L) ×155(W) ×95 (H) mm³, 1.5kg</p>	<p>133 (L) ×130(W) ×65 (H) mm³, 1.2kg</p>	<p>100 (L) ×60(W) ×56 (H) mm³, 0.2kg</p>