

MLL-N-1342/2~3.5W



**LOW NOISE INFRARED LASER
AT 1342 nm**

All solid state low noise infrared laser at 1342 nm is made features of ultra compact, long lifetime and easy operating, which is used in scientific experiment, optical instrument, optical sensor, measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	1342 ± 1	
Operating mode	CW	
Output power (W)	>2, 2.5, ... , 3.5	
Power stability (rms, over 4 hours)	<5%, <3%, <2%, <1%	
Transverse mode	Near TEM ₀₀	
Noise of amplitude(rms,20Hz~20MHz)	<1%	
M ² factor	3~6	
Beam divergence, full angle (mrad)	<3.0	
Beam diameter at the aperture (1/e ² , mm)	~3	
Warm-up time (minutes)	<15	
Polarization ratio	>50:1(100:1 Optional) , Horizontal(Vertical Optional)	
Beam height from base plate (mm)	68.4	
Pointing stability after warm-up (mrad)	<0.05	
Operating temperature (°C)	10~35	
Power supply (90-264VAC)	PSU-H-LED	PSU-H-FDA
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional	
Expected lifetime (hours)	10000	
Warranty period	1 year	



MLL-N-1342	PSU-H-LED	PSU-H-FDA
<p>245 (L) × 99 (W) × 94 (H) mm³, 2.6 kg</p>	<p>275.5 (L) × 145 (W) × 106 (H) mm³, 2.5 kg</p>	<p>275.5 (L) × 145 (W) × 106 (H) mm³, 2.5 kg</p>