

MLL-T-1064/1~10W




LD PUMPED ALL-SOLID-STATE INFRARED LASER AT 1064 nm

All solid state infrared low noise laser at 1064 nm is made features of ultra compact, long lifetime and easy operating, which is used in scientific experiment, optical instrument, optical sensor, measurement, communication, spectrum analysis, etc.




SPECIFICATIONS

Wavelength (nm)	1064±1
Operating mode	CW
Output power (W)	>1, 2, 3, ..., 10
Power stability (rms, over 4 hours)	<3%, <2%, <1%
Transverse mode	TEM ₀₀
Spectral linewidth (nm)	<0.02
Noise of amplitude (rms, 20Hz~20MHz)	<1%
M ² factor	<1.2
Beam divergence, full angle (mrad)	<1.2
Beam diameter at the aperture (1/e ² , mm)	~1.5
Warm-up time (minutes)	<10
Beam height from base plate (mm)	110
Polarization ratio	>50:1(100:1 Optional), Horizontal(Vertical Optional)
Cooled method	Air cooled
Operating temperature (°C)	10~35
Power supply (90-264VAC)	PSU-W-LED/PSU-W-FDA
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty period	1 year




MLL-T-1064




510 (L) × 190 (W) × 145 (H) mm³, 16.0kg

PSU-W-LED



342.1 (L) × 168 (W) × 143.4 (H) mm³, 4.2 kg

PSU-W-FDA



329.1 (L) × 168 (W) × 123 (H) mm³, 4.1 kg