

MLL-V-1064/6~20W




**LOW NOISE INFRARED LASER
AT 1064 nm**

All solid state low noise infrared laser at 1064 nm is made features of ultra compact, long lifetime and easy operating, which is used in scientific experiment, optical instrument, optical sensor, measurement, communication, spectrum analysis, etc.




SPECIFICATIONS

Wavelength (nm)	1064±1
Operating mode	CW
Output power (W)	>6, 6.5, 7, ..., 20
Power stability (rms, over 4 hours)	<5%, <3%, <2%, <1%
Transverse mode	TEM ₀₀
Noise of amplitude (rms, 1Hz~20MHz)	<1%, <2%, <3%
M ² factor	<2.0
Beam divergence, full angle (mrad)	<2.0
Beam diameter at the aperture (1/e ² , mm)	<2.0
Warm-up time (minutes)	<10
Beam height from base plate (mm)	113
Polarization ratio	>100:1
Operating temperature (°C)	10~35
Power supply (90-264VAC)	PSU-Z-LED
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty period	1 year




MxL-V-1064



420 (L) × 142 (W) × 144 (H) mm³, 9.5 kg

PSU-Z-LED



320 (L) × 300 (W) × 123 (H) mm³, 5.2 kg