

MPL-III-1319/10~15uJ/1-100mW

LD PUMPED ALL-SOLID-STATE Q-SWITCHED LASER




All solid state Q-switched laser at 1319nm has the features of high peak power, high repetition rate, and short pulse duration, which is widely used in industry (marking on the diamond or stone), teaching of nonlinear optics, fiber communication, etc.



SPECIFICATIONS

Wavelength (nm)		1319±1
Operating mode		Q-switched pulsed laser
Single pulse energy (μJ)		10~15
Pulse duration (ns)		~10
Peak power (W)		~1000
Rep. rate (kHz)	Controllable	Specified One rep. rate, such as 1k, 2k, 3k, up to 5kHz, with stable laser pulses emitting (stable pulse energy, peak, duration and period). Different rep. rate in the range of 1Hz-5kHz can be obtained by input an external TTL signal.
	Uncontrollable	Undefined rep. rate among 5k-20kHz and unstable laser pulse emitting. Suitable for the applications only needing high peak power pulses.
Average power (mW)		Average power (mW) = Single pulse energy (μJ) * Rep. rate (kHz)
Ave power stability (over 4 hours)		<1%, <3%, <5%
Transverse mode		TEM ₀₀
Warm-up time (minutes)		<10
M ² factor		<1.2
Beam divergence, full angle (mrad)		<1.5
Beam diameter at the aperture (mm)		~2.0
Beam height from base plate (mm)		24.8
Operating temperature (°C)		10~35
Power supply (90-264VAC)		PSU-III-FDA
Expected lifetime (hours)		10000
Warranty		1 year



MxL-III-1319	Dimensions	PSU-III-FDA	Dimensions
 <p>140.8(L)×73(W)×46.2(H) mm³, 0.6kg</p>		 <p>133 (L) ×130(W) ×65 (H) mm³, 1.2kg</p>	