

长春新产业光电技术有限公司

Changchun New Industries Optoelectronics Tech. Co., Ltd.

DATA SHEET

MRL-FN-679/1~30mW



LD PUMPED ALL-SOLID-STATE RED LASER AT 679nm

All solid state 679nm red laser is made features of ultra compact, long lifetime, low cost and easy operating, which is widely used in measurement, spectrum analysis, and laser lighting show etc.









SPECIFICATIONS

Central wavelength (nm)	679±1
Operating mode	CW
Output power (mW)	>1,10,20,30
Power stability (rms, over 4 hours)	<2%,<3%,<5%
Transverse mode	TEM ₀₀
M ² factor	<1.5
Beam diameter at the aperture (1/e², mm)	<1.0
Beam divergence, full angle (mrad)	<1.5
Polarization ratio	> 100:1 Horizontal±5 degree (Vertical Optional)
Warm-up time (minutes)	<10
Pointing stability after warm-up (mrad)	<0.05
Beam height from base plate (mm)	27.4
Operating temperature (°C)	10~35
Power supply (90-264VAC)	PSU-H-LED/PSU-H-FDA
Expected lifetime (hours)	10000
Warranty	1 year





Note: The laser head needs to be used on a heat sink with good heat dissipation.

