



MRL-III-660L/1~180mW



RED DIODE LASER
AT 660nm

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in measurement, spectrum analysis, laser lighting show, etc.



SPECIFICATIONS

Central wavelength (nm)	660±5
Operating mode	CW
Output power (mW)	>1,10,20,..., 180
Power stability (rms, over 4 hours)	<1%, <2%, <3% (<0.5%, optional)
Transverse mode	Near TEM ₀₀
M ² factor	<1.5 (<1.2, optional)
Beam diameter at the aperture (1/e ² ,mm)	~3.0 (~1.2, optional)
Beam divergence, full angle (mrad)	<1.0
Polarization ratio	>50:1 (>100:1, optional) Horizontal±5 degree (Vertical Optional)
Warm-up time (minutes)	<5
Pointing stability after warm-up (mrad)	<0.05
Beam height from base plate (mm)	24.8
Operating temperature (°C)	10~35
Power supply	85-264VAC PSU-III-LED/ PSU-III-FDA (Frequency for 1Hz-30kHz)
	100-240VAC PSU-A-D (Frequency for 30kHz -100kHz)
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz, 30kHz-100kHz optional
Expected lifetime (hours)	10000
Warranty	1 year



MRL-III-660L	PSU-III-LED	PSU-III-FDA	PSU-A-D
<p>143.5(L)×73(W) ×46.2(H) mm³, 0.7kg</p>	<p>188.6 (L) ×155(W) ×92 (H) mm³, 1.5kg</p>	<p>171(L) ×130(W) ×62.2 (H) mm³, 1.2kg</p>	<p>162(L) ×144(W) ×70 (H) mm³, 1.0kg</p>