



MRL-H-722/1~50mW

**LD PUMPED ALL-SOLID-STATE
RED LASER AT 722nm**





All solid state 722nm red laser is made features of ultra compact, long lifetime, low cost and easy operating, which is widely used in measurement, spectrum analysis, and scientific experiment, etc.



SPECIFICATIONS

Wavelength (nm)	722 ± 1		
Output power (mW)	>1, 5, 10, 20, ... , 50		
Transverse mode	TEM ₀₀		
Operating mode	CW		
Power stability (rms, over 4 hours)	<5%, <10%		
Warm-up time (minutes)	<10		
M ² factor	<1.2		
Beam divergence, full angle (mrad)	<1.5		
Beam diameter at the aperture (mm)	~2.0		
Beam height from base plate (mm)	29		
Polarization ratio	>100:1 (0 or 90 degree)		
Pointing stability after warm-up (mrad)	<0.05		
Operating temperature (°C)	10~35		
Power supply (90-264VAC)	PSU-H-LED	PSU-H-FDA	PSU-H-OEM
Expected lifetime (hours)	10000		
Warranty	1 year		



MxL-H-722	PSU-H-LED	PSU-H-FDA	PSU-H-OEM
 155(L)×77(W)×60(H) mm ³ , 0.9 kg	 268 (L) ×145(W) ×106 (H) mm ³ , 2.6 kg	 238 (L) ×146(W) ×102 (H) mm ³ , 2.3 kg	 238 (L) ×146(W) ×94 (H) mm ³ , 2.2 kg
