



MRL-III-FS-655/1000~1500mW

**RED DIODE LASER
At 655nm**





Diode red laser 655nm is made features of ultra compact, long lifetime, low cost and easy operating, which is widely used in measurement, spectrum analysis, laser lighting show, etc.



SPECIFICATIONS

Wavelength (nm)	655 ± 10		
Output power (mW)	>1000, 1100, 1200, ... , 1500		
Transverse mode	Near TE ₀₀		
Operating mode	CW		
Power stability (rms, over 4 hours)	<1%, <3%, <5%		
Warm-up time (minutes)	<5		
M ² factor	<20		
Beam divergence, full angle (mrad)	<2.5		
Dimensions of beam at the aperture (mm)	~4×9		
Beam height from base plate (mm)	28.5		
Polarization ratio	>50:1		
Pointing stability after warm-up (mrad)	<0.05		
Operating temperature (°C)	10~35		
Power supply (90-264VAC or 5VDC)	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
TTL / Analog modulation	Optional, 2kHz or higher (on request, up to 30kHz)		
Expected lifetime (hours)	10000		
Warranty	1 year		
Remarks	MRL-655 is a diode laser module, so the beam quality is not as good as the solid-state laser at 671nm. The beam spot is nearly square.		



MxL-III-FS-655	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
 <p>136(L)×73(W)×50(H) mm³, 0.6kg</p>	 <p>154 (L) ×155(W) ×95 (H) mm³, 1.5kg</p>	 <p>133 (L) ×130(W) ×65 (H) mm³, 1.2kg</p>	 <p>100 (L) ×60(W) ×56 (H) mm³, 0.2kg</p>
