



MRL-III-FS-655/1~1300mW

**RED DIODE LASER
At 655nm**

Red diode laser module at 655nm is made features of ultra compact, long lifetime, low cost and easy operating, which is widely used in measurement, spectrum analysis, laser lighting show, etc.



SPECIFICATIONS

Wavelength (nm)	655±10	
Operating mode	CW	
Output power (mW)	>1, 100, 200, ... , 1300	
Power stability (rms, over 4 hours)	<1%, <3%, <5%	
Transverse mode	Multimode	
Beam diameter at the aperture (mm)	~4×9	
Beam divergence, full angle (mrad)	<2.5	
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	28.5	
Operating temperature (°C)	10~35	
Power supply (85-264VAC)	PSU-III-LED	PSU-III-FDA
TTL / Analog modulation	TTL or Analog with 1Hz-1KHz 1KHz-10KHz, 10KHz-30KHz optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



MxL-III-FS-655	PSU-III-LED	PSU-III-FDA
<p>146(L)×73(W)×50(H) mm³, 0.7kg</p>	<p>188.6 (L) ×155(W) ×92 (H) mm³, 1.5kg</p>	<p>171(L) ×130(W) ×62.2 (H) mm³, 1.2kg</p>