

MSL-FN-607/1~100mW



SINGLE LONGITUDINAL MODE GREEN LASER AT 607nm

All solid state red at 607nm is made features of ultra compact, long lifetime and easy operating, which is widely used in measurement, spectrum analysis as the substitute for He-Ne lasers.



SPECIFICATIONS

Wavelength (nm)	607±1
Operating mode	CW
Output power (mW)	>1, 5, 10, 20, ... , 100
Power stability (rms, over 4 hours)	<1%, <2%, <3%
Transverse mode	TEM ₀₀
Longitudinal mode	Single
Spectral linewidth (nm)	<0.00001
Coherent length (m)	>50
Noise of amplitude (rms, 1Hz~20MHz)	<1%
M ² factor	<1.2
Beam diameter at the aperture (1/e ² , mm)	<1.5
Beam divergence, full angle (mrad)	<1.2
Polarization ratio	>100:1, Vertical±5 degree (Horizontal Optional)
Warm-up time (minutes)	<10
Pointing stability after warm-up (mrad)	<0.05
Beam height from base plate (mm)	27.4
Operating temperature (°C)	15~35
Power supply (90-264VAC)	PSU-H-FDA
Expected lifetime (hours)	10000
Warranty	1 year



Note: The laser head needs to be used on a heat sink with good heat dissipation.

MSL-FN-607	PSU-H-FDA
<p style="text-align: center;">197(L)×70(W)×50(H) mm³, 1.5 kg</p>	<p style="text-align: center;">275(L) ×145(W) ×104(H) mm³, 2.3 kg</p>