



MxL-S-SM-xxx /1~500mW

SPECIFICATIONS

SM FIBER OUTPUT LASER

CNI has a long experience in the delivery of fiber coupled laser light sources providing high efficiency and long term stability. All laser types can be offered with appropriate fiber coupling systems. This type is specifically designed for single-mode fiber(include PM) coupling with high power stability and long term stability.



Wavelength (nm)	473±1	532±1	589±1	671±1	1064±1
Operating mode	CW				
Output power (mW)	>1 ,...,50	>1, ...,150	>1, ...,20	>1, ...,100	>1, ...,500
Power stability (rms, over 4 hours)	<2%, <3%, <5%	<1%, <2% <3%, <5%	<3%, <5%	<2%, <3%, <5%	<2%, <3%, <5%
Transverse mode	TEM ₀₀ (single mode fiber output)				
Fiber numerical aperture	0.10~0.12				
Fiber type	SM fiber (PM fiber optional)				
Fiber connector	FC				
Fiber jacket	PVC (black)				
Polarization ratio	No polarization (>50:1 after PM fiber)				
Warm-up time (minutes)	<10				
Operating temperature (°C)	10~35				
Power supply (90-264VAC or 5VDC)	PSU-III-LED/PSU-III-FDA/PSU-III-OEM-97				
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option				
Expected lifetime (hours)	10000				
Warranty	1 year				



MxL-S-SM-xxx	PSU-III-LED	PSU-III-FDA	PSU-III-OEM-97
<p>151 (L) × 50 (W) × 47 (H) mm³, 0.7kg</p>	<p>188(L) × 155(W) × 92 (H) mm³, 1.5kg</p>	<p>171 (L) × 130(W) × 62.2 (H) mm³, 1.2kg</p>	<p>94(L) × 75(W) × 49(H) mm³, 0.23kg</p>