

OEM-D-532/20~30W

SPECIFICATIONS



LD PUMPED ALL-SOLID-STATE GREEN LASER




All solid state 532nm green laser is made features of ultra compact, long lifetime and easy operating, which is widely used in collimation, laser medical treatment, scientific experiment, optical instrument, laser display, laser lighting show, etc.



Wavelength (nm)	532±1
Model	OEM-D
Operating mode	CW
Output power (W)	>20, 21, ..., 30
Power stability (rms, over 4 hours)	<3%, <5%
Transverse mode	Near TEM <sub>00</sub>
Beam divergence, full angle (mrad)	<2.0
Beam diameter at the aperture (1/e <sup>2</sup> , mm)	~5.0
Warm-up time (minutes)	<10
Beam height from base plate (mm)	30
Operating temperature (°C)	22.5+/-2.5
Driver (12VDC 25A)	PSU-DEP-W-OEM
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty time	1 year



Note: The laser needs to be used on a heat sink with good heat dissipation.

OEM-D-532	PSU-DEP-W-OEM	Accessory (Power supply 100-240VAC)
 <p>319.5 (L) × 280 (W) × 68 (H) mm<sup>3</sup></p>	 <p>203 (L) × 140 (W) × 74 (H) mm<sup>3</sup>, 1.6 kg</p>	 <p>12VDC 50A: 218 (L) × 116.5 (W) × 41 (H) mm<sup>3</sup>, 1.2 kg</p>