



PGL-D12-405/1~200mW


SPECIFICATIONS




**HIGH POWER VIOLET LASER
MODULE AT 405 nm**

PGL-D12 high power blue laser module at 405nm is made features of small size, high output power, long lifetime, which made it widely used in collimation, laser medical treatment, scientific experiment, optical instrument and so on



Wavelength (nm)	405 ±5
Operating mode	CW
Output power (mW)	>1,5, 10 , ... , 200
Transverse mode	Near TEM ₀₀
Beam diameter at the aperture (1/e ² , mm)	~3.5
Beam divergence, full angle (mrad)	<0. 5
Operating temperature (°C)	15~30
Power supply	DC 6V PCB
Expected lifetime (hours)	10000
Warranty	6 months
Note: The shell has non-polarity.	



PGL-D12-405	Dimensions	6VPCB
 <p>Φ12×20(L) mm², 0.013 kg</p>		 <p>17(L) ×11(W) mm²</p>