

PGL-D8-447/1~30mW

**BLUE LASER MODULE
AT 447nm**


PGL-D8-447 is made features of wide temperature operating (no TEC), high reliability, and low cost, which is widely used in orientation, alignment and measurement, etc.



SPECIFICATIONS

Wavelength (nm)	447±10
Operating mode	CW
Output power (mW)	>1, 10, 15,...,30
Transverse mode	Near TEM ₀₀
Beam diameter at the aperture (1/e ² , mm)	~3.5
Beam divergence, full angle (mrad)	<1.0
Operating temperature (°C)	15~30
Power supply	DC 6V PCB
Expected lifetime (hours)	10000
Warranty period	6 months

Note: The shell has non-polarity.



PGL-D8-447	Dimensions	6VPCB
<p>Φ8×15(L) mm², 1.5g</p>		<p>13(L) ×10(W) mm²</p>