



PGL-III-532/5~200mW

PGL-III-C-532/200~500mW


**PORTABLE GREEN LASER
AT 532nm**






PGL-III 532nm is made features of small size, high output power, long lifetime in portable laser, and special safety design to ensure security.



SPECIFICATIONS

Model	PGL-III-532	PGL-III-C-532
Wavelength (nm)	532±1	
Operating mode	CW	
Output power (mW)	>5, 10, 15, ... , 200	>200, 250, 300, ... , 500
Transverse mode	TEM ₀₀	
Beam diameter at the aperture (1/e ² , mm)	~1.5	
Beam divergence, full angle (mrad)	<1.5	
Switch	Push button	
Surface color	Black	
Power Consumption	DC 3.0V	DC 3.6V
Power supply	2×“C”size 1.5V Alkaline batteries	1×“No. 18650” Lithium battery
Expected lifetime (hours)	5000	
Warranty	6 months	
Remark	LED indicator, remote connector and key switch are available.	



PGL-III-532	Dimensions	PGL-III-C-532	Dimensions	Accessory
 <p>Φ38×234(L) mm², 0.3 kg</p>		 <p>Φ38×220(L) mm², 0.4 kg</p>		 <p>1×“No. 18650” Li batteries and charger</p>