



PGL-III-C-520/5~500mW

**PORTABLE GREEN LASER  
AT 520nm**




PGL-III-C-520 is made features of small size, high output power, long lifetime in portable laser, and special safety design to ensure security.



**SPECIFICATIONS**

Wavelength (nm)	520±5
Operating mode	CW
Output power (mW)	>5, 10, 20, 30, ... , 500
Transverse mode	Near TEM <sub>00</sub>
Beam diameter at the aperture (1/e <sup>2</sup> , mm)	~5.0
Beam divergence, full angle (mrad)	<1.5
Operating temperature (°C)	0~40
Switch	Push button
Surface color	Black
Power Consumption	DC 6V
Power supply	2×“ CR123A 3V” Lithium batteries
Expected lifetime (hours)	5000
Warranty	6 months
Remark	LED indicator, remote connector and key switch are available.



PGL-III-C-520	Dimensions	Accessory
 <p>Φ38×224(L) mm<sup>2</sup>, 0.3 kg</p>		 <p>2×CR123A/3V lithium battery</p>