



PGL-III-1064/5~500mW

PGL-III-C-1064/5~500mW

**PORTABLE LASER
AT 1064nm**






PGL-III-1064 is made features of small size, driven by battery, special safety parts design.



SPECIFICATIONS

Model	PGL-III-1064	PGL-III-C-1064
Wavelength (nm)	1064 ± 1	
Output power (mW)	>5, 10, 20, 30, ..., 500	>5, 10, 20, 30, ..., 500
Transverse mode	TEM ₀₀	
Operating mode	CW	
Beam divergence, full angle (mrad)	<1.5	
Beam diameter at the aperture (mm)	~1.5	
Switch	Push button	
Surface color	Black	
Range in darkness (m)	1000~10000	
Power supply	2×“C”size/1.5V batteries	1×“No. 18650” Li batteries
Expected lifetime (hours)	5000	
Warranty	6 months	
Remark	LED indicator, remote connector and key switch are available.	



<p>PGL-III-1064</p>  <p>Φ38×230(L) mm³, 0.3 kg</p>	<p>Dimensions</p> 	<p>PGL-III-C-1064</p>  <p>Φ38×220(L) mm³, 0.4 kg</p>	<p>Dimensions</p> 	<p>Accessory</p>  <p>1×“No. 18650” Li batteries and charger</p>
--	---	---	---	--