



PGL-RB-655/1~350mW

MULTICOLOR PORTABLE LASER
AT 447 & 655 nm

Portable laser PGL-RB 447&655 nm is made features of small size, high output power, long lifetime, and special safety design to ensure security, which can emit three different colors, including green, red and yellow.



SPECIFICATIONS

Model	PGL-RB	
Wavelength (nm)	447±5	655±5
Output power (mW)	1~200mW, optional	1~150mW, optional
Operating mode	CW	
Beam divergence, full angle (mrad)	<1.2	
Beam diameter at the aperture (mm)	~4	
Switch	Push button	
Surface color	Black	
Power supply	2×“ Cr123A” Li batteries	
Expected lifetime (hours)	5000	
Warranty	6 months	
Remark	LED indicator, remote connector and key switch are available.	



Dimensions	PGL-RB (Blue light)	PGL-RB (Red light)	PGL-RB (Pink light)	Accessory
<p>Φ40×204(L) mm³, 0.3 kg</p>				<p>2×CR123A/3V lithium battery</p>