




Features:

- ◆ Multi-channel independent control output
- ◆ High brightness, high efficiency
- ◆ Precise adjustment of brightness
- ◆ Support TTL control output
- ◆ Customizable

Model	SLE-IV-B
Channel	4
Wavelength range	375-640nm
LED Peaks	385nm/460nm/555nm/625nm
Lifetime	20000h
Output Power	950mW@385nm 3200mW@460nm 1600mW@555nm 780mW@625nm (Output power per source channel is dependent on filter bandpass)
Control Mode	Four independent controls, 0~100% dimming, accuracy of 1%
ON/OFF Response Times	Rising/ Descending Edge (10%~90%) < 50us
Operating Mode	Continuous Output, Default TTL Modulation (Analog Modulation Optional)
Control Mode	Support RS232 host computer control
Control Options	SMA - External trigger TTL signal (external trigger analog modulation optional) Serial Interface (RS232) - Light Output ON/OFF and brightness adjusting Manual control box (optional) - Light Output ON/OFF and brightness adjusting
Operating Temperature	10~35°C
Power Input	DC12V
Cooled Method	Air Cooled
Warranty	1 Year
Size	263.2mm×192.5mm×74mm (Reference)

Spectrogram:



Dimensions:

