



UV-F-360 /1~100mW



**LD PUMPED ALL-SOLID-STATE  
UV LASER AT 360nm**

All solid state 360nm UV laser is made features of ultra compact, long lifetime, cost-effectiveness and easy operating, which is used in DNA sequencing, flow cytometry, cell sorting, optical instrument, measurement, physics experiment, laser rapid modeling, Raman spectroscopy and fluorescence analysis etc.



SPECIFICATIONS

Central wavelength (nm)	360±1
Operating mode	CW
Output power (mW)	>1, 10, 20, ... , 100
Power stability (rms, over 4 hours)	<1%, <2%, <3%, <5%
Transverse mode	Near TEM <sub>00</sub>
M <sup>2</sup> factor	<2.0
Beam diameter at the aperture (1/e <sup>2</sup> , mm)	~1.2
Beam divergence, full angle (mrad)	<1.0
Polarization ratio	>50:1 Horizontal±5 degree (Vertical Optional)
Warm-up time (minutes)	<10
Beam height from base plate (mm)	45
Operating temperature (°C)	10~35
Power supply (90-264VAC)	PSU-H-LED/PSU-H-FDA
Expected lifetime (hours)	5000
Warranty	1 year



UV-F-360	PSU-H-LED	PSU-H-FDA
<p>211 (L)×88(W)×74(H) mm<sup>3</sup>, 1.6 kg</p>	<p>277 (L)×145(W)×106 (H) mm<sup>3</sup>, 2.6 kg</p>	<p>275(L)×145(W)×104(H) mm<sup>3</sup>, 2.3 kg</p>