

YL-I-520 1~10W

DIODE LASER AT 520nm

Diode laser 520nm is made features of ultra compact, long lifetime, low cost and easy operating. It's easy to be installed in customer's equipment.





SPECIFICATIONS

Wavelength (nm)	520±5
Operating mode	CW
Output power (W) @ after 400um fiber	1~10
Fiber Core Diameter (um)	100, 200, 400, 600
Fiber Connector	SMA905/ FC
Numerical Aperture (NA)	0.22
Fiber length (m)	1 (Fiber length can be customized)
Power stability (rms, over 4 hours)	<1%
Cooled method	With TEC/ without TEC optional
Warm-up time (minutes)	<5
Operating temperature (°C)	25+/-3
Expected lifetime (hours)	10000
Warranty	1 year





Dimensions of Laser head (Without TEC)





1-4W

103.6 (L)*55 (W)*26 (H) mm³



5-7W



113.5 (L)*68 (W)*26 (H) mm³



8-10W


142.5 (L)*68 (W)*26 (H) mm³

Dimensions of Laser head (With TEC)




1-4W

103.6 (L)*55 (W)*32 (H) mm³



5-7W


113.5 (L)*68 (W)*32 (H) mm³





8-10W

142.5 (L)*68 (W)*32 (H) mm³



Driver (Optional)



140 (L)*110 (W)*24 (H) mm³




143 (L)*127.7 (W)*49.3 (H) mm³




276.2 (L)*145 (W)*106 (H) mm³

A heat dissipation




140 (L)*110 (W)*67 (H) mm³



120 (L)*66 (W)*60 (H) mm³

FC-W



264 (L)*288 (W)*149 (H) mm³