

FS-H-515A/1-100mW

## FEMTOSECOND PULSED LASER AT 515nm

All Fiber Femtosecond pulsed laser at 515nm is made features of short pulse duration, high repetition rate, high stability and good beam quality, which is used in optical microscope, photon imaging, physics experiment, etc.




### SPECIFICATIONS

Wavelength (nm)	515±5
Operating mode	Pulsed
Average power (mW) <sup>1</sup>	1-100
Single pulse energy (nJ)	1-1.25
Rep. rate (MHz)	80±1
Pulse duration (fs)	<150
Peak power (kW)	1-7.5
Ave power stability (rms, 4 hours±3°C)	<2%, <1%
Warm-up time (minutes)	<10
Transverse mode	TEM <sub>00</sub>
Beam divergence, full angle (mrad)	<1.0
Beam diameter at the aperture (1/e <sup>2</sup> ,mm)	<2
M <sup>2</sup> factor	<1.2
Beam height from base plate (mm)	98
Cooled method	Air cooled
Operating temperature (°C)	10-35
Power supply (100-240VAC)	12V/6.67A
Expected lifetime (hours)	>10000




### LASER HEAD (DRIVER Integrated)



309 (L)×244 (W) ×124(H) mm<sup>3</sup>,7.5kg

### POWER SUPPLY(100-240VAC)optional



145 (L) ×60 (W) ×32 (H) mm<sup>3</sup>,1.2 kg

<sup>1</sup> One fixed value between 1-100mW.