



MDL-III-965/1~2000mW

**INFRARED DIODE LASER
AT 965nm**





Diode infrared laser module at 965nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	965±5		
Output power (mW)	>1, 100, 200, 300, ..., 2000		
Transverse mode	Multimode		
Operating mode	CW		
Power stability (rms, over 4 hours)	<1%, <3%, <5%		
Warm-up time (minutes)	<5		
M ² factor	<20		
Beam divergence, full angle (mrad)	<3.0		
Dimensions of beam at the aperture (mm)	~5×8		
Beam height from base plate (mm)	24.8		
Polarization ratio	>50:1		
Operating temperature (°C)	10~35		
Power supply (90-264VAC or 5VDC)	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
Modulation option	TTL/Analog 1Hz-5KHz, 1Hz-10KHz, 1Hz-30KHz, and TTL on/off		
Expected lifetime (hours)	10000		
Warranty	1 year		



MxL-III-965	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
 136(L)×73(W)×46.2(H) mm ³ , 0.6kg	 153 (L) ×155(W) ×92 (H) mm ³ , 1.5kg	 133 (L) ×130(W) ×65 (H) mm ³ , 1.2kg	 100 (L) ×62(W) ×56 (H) mm ³ , 0.2kg
