



MDL-NS-375/1-100mW




**NANOSECOND PULSED
VIOLET DIODE LASER
AT 375nm**

This series laser products with excellent material removal rate, are widely used in microelectronics, material processing, solar energy and medical equipment manufacturing, etc.



SPECIFICATIONS

Central wavelength (nm)	375±5	
Operating mode	Pulsed	
Peak power (mW) ¹	1-50	50-100
Power stability (rms, 4 hours ± 3°C)	<2%, <1%, <0.5%	
Pulse width (FWHM)	10ns-10ms	
Transverse mode	Near TEM ₀₀	Multimode
Beam diameter at the aperture (1/e ² , mm)	~3.0	<1.5×3.5
Beam divergence, full angle (mrad)	<0.5	~2.3×0.2
Polarization ratio	>50:1, (>100:1 optional) Horizontal±5 degree (Vertical optional)	
Rep. rate ²	DC-25MHz	
Rise Time (ns)	<4	
Fall Time (ns)	<3	
Modulation Depth (extinction ratio)	>1000000:1	
Warm-up time (minutes)	<5	
Cooled method	Conduction	
Beam height from base plate (mm)	19	
Operating temperature (°C)	10-35	
Operating voltage (VDC)	12V/3.34A	
Expected lifetime (hours)	>10000	



LASER HEAD (DRIVER Integrated) ³	POWER SUPPLY (100-240VAC) optional	MULTIFUNCTIONAL PULSE TRIGGER optional
<p>112 (L) × 60 (W) × 50 (H) mm³, 0.5kg</p>	<p>125.7 (L) × 50.2 (W) × 31.8 (H) mm³, 0.3kg</p>	<p>150 (L) × 105 (W) × 34 (H) mm³, 0.5kg</p>

1 Any power level can be selected in this range.

2 Both internal and external triggers are acceptable. The internal trigger supports a frequency range of DC-25MHz.

3 RS232 control optional, output power adjustable 10-100% by software.