

MDL-NS-785/1~100mW




**NANOSECOND PULSED  
INFRARED DIODE LASER  
AT 785nm**




This series laser products with excellent material removal rate, are widely used in microelectronics, material processing, solar energy and medical equipment manufacturing, etc.



SPECIFICATIONS

Central wavelength (nm)	785±5
Output power@3.3VDC (mW, CW)	>1, 10, 20, ...,100
Power stability (rms, over 4 hours)	<1%, <2%, <3%
Pulse width (FWHM)	>10ns, 20ns, ...,10ms
Transverse mode	Near TEM <sub>00</sub>
Noise of amplitude(rms, CW)	<1%
M <sup>2</sup> factor	<1.5
Beam diameter at the aperture (1/e <sup>2</sup> ,mm)	~4.0
Beam divergence, full angle (mrad)	<1.0
User trigger frequency (Multifunctional Pulse Trigger optional)	1Hz-30MHz (1Hz-25MHz by using CNI Multifunctional Pulse Trigger)
Rise Time (ns)	<4
Fall Time (ns)	<3
Modulation Depth (extinction ratio)	>1000000:1
Warm-up time (minutes)	<5
Beam height from base plate (mm)	19
Operating temperature (°C)	10~35
Input voltage	+12VDC
Maximum bandwidth (MHz)	>30
Expected lifetime (hours)	10000
Warranty	1 year



MDL-NS-785	Optional Power Supply	Multifunctional Pulse Trigger
 <p>112(L) × 60(W) × 50(H) mm<sup>3</sup>, 0.5kg</p>	 <p>121(L) × 50(W) × 30.8(H) mm<sup>3</sup>, 0.3kg</p>	 <p>150(L) × 105(W) × 34(H) mm<sup>3</sup>, 0.5kg</p>