



MGL-FN series (570-599nm)








LD PUMPED ALL-SOLID-STATE LASER

All solid state laser is made features of high output power stability, good beam profile, ultra compact, long lifetime and easy operating, which is widely used in collimation, laser medical treatment, scientific experiment, optical instrument, etc.



SPECIFICATIONS

Part number	MGL-FN-577	MGL-FN-588	MGL-FN-589	MGL-FN-594
Wavelength (nm)	577±2	588±1	589±1	594±1
Operating mode	CW			
Output power (mW) ¹	600-1200	300-800		1-100
Power stability (rms, 4 hours±3℃)	<3%, <2%, <1%	<2%, <1%, <0.5%		<3%, <2%, <1%
Transverse mode	TEM _{n1}	TEM ₀₀		
M ²	<2.0	<1.5		
Beam diameter at the aperture (1/e ² , mm)	<2.5	<1.5		
Beam divergence, full angle (mrad)	<1.5			
Polarization Ratio	>100:1, Horizontal (Vertical optional)			
Warm-up time (minutes)	<5			
Pointing Stability(μrad) (over 2 hours after warm-up and ±3℃)	<50			
Pointing Stability Over Temperature(μrad/℃)	<8			
Beam height from base plate (mm)	27.4			
Operating Temperature (℃)	10-35			
Modulation optional	DC-1kHz, 1kHz-10kHz, 10kHz-30kHz optional; TTL and Analog optional			
Power supply (100-240VAC)	PSU-H-FDA/PSU-H-LED/PSU-SR			
Expected lifetime (hours)	>10000			

LASER HEAD ²	HEATSINK(OPTIONAL TC-02-FS)	
 197(L)×70(W)×50(H) mm³, 1.5 kg		 220(L)×110(W)×47.5(H) mm³, 1.25 kg
POWER SUPPLY (PSU-H-FDA) ³	POWER SUPPLY (PSU-H-LED) ⁴	POWER SUPPLY (PSU-SR) ⁴
 276.6(L) ×145(W) ×103.6(H) mm³, 2.3 kg	 273.6 (L) ×145(W) ×106 (H) mm³, 2.3 kg	 188(L) ×145(W) ×83(H) mm³, 1.2kg

- 1.Any power level can be selected in this range.
- 2.The laser head needs to be used on a heat sink with good heat dissipation.
- 3.Fixed output power.
- 4.Output power adjustable 10-100%; RS232 control optional.