



MLDP-405-200-MM

■ Features

405nm
CW Mode
Coaxial or B1 Package
High stability



■ Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Reverse Voltage	Vr	2.0	V
Operating Temperature	Top	0 ~ +40	°C
Storage Temperature	Tstg	-40 ~ +85	°C
Lead Soldering Temperature (10sec)	Tis	260	°C

■ Initial Electrical/Optical Characteristics

Item	Symbol
Center Wavelength @ 25°C	405±5nm
Spectral Width (FWHM)	2.0nm
Output Power	200mW
Fiber Type	UV MM Fiber
Fiber Core	105um
Recommend Operating Temperature	25°C
Fiber Connector	FC/SC/SMA905
Fiber Length	80cm
Threshold Current (Typ.)	140mA
Operating Current (Typ.)	350mA
Operating Voltage	4.8V
Package Style	Coaxial or B1

CHANGCHUN NEW INDUSTRIES
OPTOELECTRONICS TECH.CO.,LTD.

CHANGCHUN NEW INDUSTRIES
OPTOELECTRONICS TECH.CO.,LTD.




electronics Tech. Co., Ltd ◆ CONTACT

No.888, Jinhu Road, High-tech Zone, Changchun
130103, China


Phone: +86-431-87033597

Fax: +86-431-87033597


Coaxial Package View



B1 Package View



PIN Bottom View



1	LD(+)
2	LD(-)

