



## MLDP-980-100-MM

### ■ Features

980nm  
MM Fiber  
Coaxial or B2 Package  
Built-in PD



### ■ Absolute Maximum Ratings

| Parameter                          | Symbol           | Value     | Unit |
|------------------------------------|------------------|-----------|------|
| Reverse Voltage                    | V <sub>r</sub>   | 2.0       | V    |
| Operating Temperature              | Top              | -10 ~ +40 | °C   |
| Storage Temperature                | T <sub>stg</sub> | -15 ~ +85 | °C   |
| Lead Soldering Temperature (10sec) | T <sub>is</sub>  | 260       | °C   |

### ■ Initial Electrical/Optical Characteristics

| Item                            | Symbol        |
|---------------------------------|---------------|
| Center Wavelength @ 25°C        | 980±10nm      |
| Spectral Width(FWHM)            | 2.0nm         |
| Output Power                    | 100mW         |
| Fiber Type                      | MM Fiber      |
| Fiber Core                      | 105um         |
| Recommend Operating Temperature | 25°C          |
| Monitor Current                 | 2mA           |
| PD Reverse Voltage              | 30V           |
| Fiber Connector                 | FC/SC/SMA905  |
| Fiber Length                    | 80cm          |
| Threshold Current (Typ.)        | 55mA          |
| Operating Current (Typ.)        | 350mA         |
| Operating Voltage               | 1.6V          |
| Package Style                   | Coaxial or B2 |

CHANGCHUN NEW INDUSTRIES  
OPTOELECTRONICS TECH.CO.,LTD.

CHANGCHUN NEW INDUSTRIES  
OPTOELECTRONICS TECH.CO.,LTD.



electronics Tech. Co., Ltd ◆ CONTACT

No.888, Jinhu Road, High-tech Zone, Changchun  
130103, China

Phone: +86-431-87033597

Fax: +86-431-87033597

|   |             |
|---|-------------|
| 1 | LD(-)       |
| 2 | LD(+)&PD(-) |
| 3 | PD(+)       |



CHANGCHUN NEW INDUSTRIES  
OPTOELECTRONICS TECH CO., LTD.