



MLL-III-750/1~2000mW



**LOW NOISE RED DIODE
LASER AT 750nm**

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in measurement, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	750±10	
Operating mode	CW	
Output power (mW)	>1, 100, 200, ..., 2000	
Power stability (rms, over 4 hours)	<1%, <2%, <3% (<0.5%, optional)	
Transverse mode	Multimode	
Noise of amplitude(rms,20Hz~20MHz)	<1%	
Dimensions of beam at the aperture (mm)	~5×8	
Beam divergence, full angle (mrad)	<3	
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	24. 8	
Operating temperature (°C)	10~35	
Power supply	85-264VAC	PSU-III-LED/ PSU-III-FDA (Frequency for 1Hz-30kHz)
	100-240VAC	PSU-A-D (Frequency for 30kHz -100kHz)
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz, 30kHz-100kHz optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



MLL-III-750	PSU-III-LED	PSU-III-FDA	PSU-A-D
<p>146 (L) ×73(W) ×46.2 (H) mm³, 0.7kg</p>	<p>188.6 (L) ×155(W) ×92 (H) mm³, 1.5kg</p>	<p>171(L) ×130(W) ×62.2 (H) mm³, 1.2kg</p>	<p>162(L) ×144(W) ×70 (H) mm³, 1.0kg</p>