

Laser Power Meter



Features:

Wavelength range: 200 -1100nm

Power range: 1nW-1000mW

Active area diameter: 9.5mm

SMA905/FC fiber connector (Optional)


PD1000-200-TP100

SPECIFICATIONS

Power Meter	TP100
Photodiode Power Sensor	PD1000-200
Max. Measurable Power(With Attenuator)	1000mW
Max. Measurable Power(Without Attenuator)	10mW
Min. Measurable Power	1nW
Active Area Diameter	9.5mm
Detector Material	Si
Wavelength Range	200-1100nm
Max. Power Density(With Attenuator) a*	20W/cm ²
Max. Power Density(Without Attenuator) a*	1W/cm ²
Measurement Uncertainty	±2%
Resolution	1nW
Sensitivity	1nW
Accuracy	< ±2%
Power Supply	18650(2batteries)
Computer Interface	USB 1.1 and USB 2.0
Instrument Power	-100-240 VAC, 50/60 Hz, DC 12V-3.34A
Temperature(Operating)	5° C - 45° C (41° F - 113° F)
Temperature(Storage)	-20° C - 70° C (-4° F - 158° F)
Datasheet	1 year

a*: Before testing, please pay attention to the spot size and calculate the maximum average power density. These two parameters must be within the range of the above table. If the probe is damaged due to parameters beyond the range of above table, it is not covered by the warranty.

Power Meter TP100



Photodiode Power Sensor PD1000-200

