

Laser Power Meter



PD3000-350-USB

Features:

Wavelength range: 350-1100nm

Power measurement range: 1uW-3000mW

Single channel/ multi-channel power measurement

PC upper computer software display measurement

SPECIFICATIONS

Model	PD3000-350-USB
Power Range	1uW-3000mW
Sensitivity Diameter	12mm
Probe Material	Si
Wavelength Range	350-1100nm
Measurement Uncertainty	$\pm 2\%$
Resolution	1uW
Sensitivity	1uW
Accuracy	$< \pm 2\%$
Computer Interface	USB 1.1 and USB 2.0
Temperature (Operating)	5°C - 45°C (41°F - 113°F)
Temperature (Storage)	-20°C - 70°C (-4°F - 158°F)
Warranty Period	1 year

a*: Before testing, please pay attention to the spot size and calculate the maximum average power density. These two parameters must be within the range of the above table. If the probe is damaged due to parameters beyond the range of above table, it is not be covered by the warranty.

PD3000-350-USB

