



PGL-VI-561



PGL-VI green laser module at 561nm is made features of small size, high output power, long lifetime, which made it be used widely in collimation, laser medical treatment, scientific experiment, optical instrument and so on.

SYSTEM SPECIFICATIONS*

Wavelength	nm	561
Wavelength tolerance	nm	±5
Output power	mW	1-5
Operating mode		CW
Transverse mode		TEM ₀₀
Beam diameter at the aperture(1/e ²)	mm	~1.5
Beam divergence, full angle	mrad	<1.5
Expected lifetime	hours	10000
Warranty	years	1

ELECTRICAL SPECIFICATIONS

Operating voltage(internal PCB)	3VDC
Operating voltage(external PCB)	3VDC
Connection	Cable with flying leads

ENVIRONMENTAL CONDITIONS

Operating temperature	10°C to 35°C
Storage temperature	-20°C to 80°C
Humidity	<90%, non-condensing
Dissipated heat	<6W


MECHANICAL SPECIFICATIONS

Dimensions of PGL-VI-561	Φ20×100mm ²
Dimensions of PGL-VI-1-561	Φ15×65mm ²
Material	Aluminum/Copper
Shell polarity	The housing has a positive electrode.


*All testing data under the conditions of temperature 25°C.




Dimensions of PGL-VI-561(Internal PCB, $\Phi 20 \times 100 \text{mm}^2$, 3VDC)



Dimensions of PGL-VI-1-561(external PCB, $\Phi 15 \times 65 \text{mm}^2$, 3VDC)



Dimensions of external PCB($38 \times 14 \times 8 \text{mm}^3$, 3VDC, internal control 750hz frequency)



Dimensions of external PCB($19 \times 15 \times 11.2 \text{mm}^3$, 3VDC)

